

**Lewatit® MonoPlus M 800** is a strongly basic, gelular anion exchange resin with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer. Chemically and osmotically considered, the monodisperse beads are highly stable. The optimized kinetics lead to an increased operating capacity compared to ion exchange resins with heterodisperse bead size distribution.

**Lewatit® MonoPlus M 800** is especially applicable for:

- » conventional mixed bed application in combination with **Lewatit® MonoPlus S 108 H**, **Lewatit® MonoPlus S 200 H**
- » polishing by a modern Lewatit® Multistep System
- » condensate polishing in combination with **Lewatit® MonoPlus S 200 H or KR** and also **Lewatit® MonoPlus S 215 KR**

**Lewatit® MonoPlus M 800** adds special features to the resin bed:

- » high exchange flow rates during regeneration and loading
- » good utilization of the total capacity
- » low rinse water demand
- » homogenous throughput of regenerants, water and solutions; therefore a homogeneous working zone
- » nearly linear pressure drop gradient for the whole bed depth; therefore an operation with higher bed depth possible
- » good separation behavior of the components in a mixed bed application

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess Sybron Inc.

# PRODUCT INFORMATION

## LEWATIT® MonoPlus M 800



### Common Description

Delivery form	Cl <sup>-</sup>
Functional group	quaternary ammonium type 1
Matrix	styrenic
Structure	gel
Appearance	yellow, translucent

### Specified Data

		US Units		Metric Units	
Uniformity coefficient				max.	1.1
Mean bead size	d50			mm	0.60 (+-0.05)
Total capacity (delivery form)		kgr/ft <sup>3</sup>	30.6	min. eq/L	1.4

This document contains important information and must be read in its entirety.

Edition: 2017-07-25  
Previous Edition: 2017-06-14

## Typical Physical and Chemical Properties

		US Units		Metric Units	
Bulk density for shipment	(+/- 5%)	lb/ft <sup>3</sup>	41.9	g/L	670
Density				approx. g/mL	1.08
Water retention (delivery form)				approx. weight %	43-48
Volume change (Cl <sup>-</sup> -OH <sup>-</sup> )				max. approx. %	22
Stability pH range					0-14
Storage time (after delivery)				max. years	2
Storability temperature range				°C	-20 - +40

## Operation

		US Units		Metric Units	
Operating temperature		max. °F	158	max. °C	70
Operating pH range	during exhaustion				0-12
Bed depth for single column		min. inches	31.5	min. mm	800
Bed depth per component in mixed bed		min. inches		min. mm	500
Back wash bed expansion per m/h (20°C)				%	10
Specific pressure loss (15°C)				kPa*h/m <sup>2</sup>	1
Max. pressure loss during operation		PSI	36	kPa	250
Specific flow rate		max. gpm/ft <sup>3</sup>	13	max. BV/h	100

## Regeneration

		US Units		Metric Units	
NaOH regeneration	concentration	approx. wt. %		approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. lb/ft <sup>3</sup>	6.3	min. g/L resin	100
NaOH regeneration	quantity counter-current	min. lb/ft <sup>3</sup>		min. g/L resin	50
Regeneration contact time		min. minutes		min. minutes	20
Slow rinse at regeneration flow rate		min. gal/ft <sup>3</sup>	15.0	min. BV	2
Fast rinse at service flow rate		min. gal/ft <sup>3</sup>	15.0	min. BV	2

## Additional Information & Regulations

### Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

### Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

### Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

### Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

### Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described above. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

<b>Safety precautions</b>	<b>Safety precautions</b> Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.
<b>Toxicity</b>	<b>Toxicity</b> The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.
<b>Disposal</b>	<b>Disposal</b> In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.
<b>Storage</b>	<b>Storage</b> It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

# PRODUCT INFORMATION

## LEWATIT® MonoPlus M 800



**Headquarters:** 54/18 Bui Quang La, Ward 12, Go Vap District, HCMC, Viet Nam  
**Office:** 12 DHT10B, Dong Hung Thuan Ward, District 12, HCMC, Viet Nam  
**Phone:** (028) 6258 5368 - (028) 6291 9568  
**Email:** [info@atswatertechnology.com](mailto:info@atswatertechnology.com)  
**Website:** [www.atswatertechnology.com](http://www.atswatertechnology.com)

The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and application. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change with notice. It is expressly understood and agreed that you assume and hereby expressly release us from liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

**Health and Safety Information:** Appropriate literature has been assembled which provides information concerning the health and safety precautions that must be observed when handling the LANXESS Sybron Chemicals, Inc. products mentioned in this publication. For materials mentioned which are not LANXESS Sybron Chemicals, Inc. products, appropriate industrial hygiene and other safety precautions recommended by their manufacturers should be followed. Before working with any of these products, you must read and become familiar with the available information on their hazards, proper use, and handling. This cannot be overemphasized. Information is available in several forms, e.g., *material safety data sheets and product labels*. Consult your LANXESS Sybron Chemicals, Inc. representative or contact the Product Safety and Regulatory Affairs Department at LANXESS Sybron Chemicals, Inc.

**Regulatory Compliance Information:** Some of the end uses of the products described in this publication must comply with applicable regulations, such as the FDA, BfR, NSF, USDA, and CPSC. If you have any questions on the regulatory status of these products, contact – for business in the USA - the LANXESS Corporation Regulatory Affairs and Product Safety Department in Pittsburgh, PA, USA or for business outside US the Regulatory Affairs and Product Safety Department of LANXESS Deutschland GmbH in Germany.

**Note:** The information contained in this publication is current as of the date of edition. Please contact LANXESS Sybron Chemicals Inc. to determine if this publication has been revised.

### LANXESS Sybron Chemicals Inc.

200 Birmingham Road  
Birmingham, NJ 08011  
USA

+1-800-678-0020  
[lewatit@lanxess.com](mailto:lewatit@lanxess.com)

[www.lanxess.com](http://www.lanxess.com)  
[www.lpt.lanxess.com](http://www.lpt.lanxess.com)

This document contains important information and must be read in its entirety.

Edition: 2017-07-25  
Previous Edition: 2017-06-14

